


Prism Diffuser



Prism Advertisement

## Contents:

- Prism User Guide Intro..... Page 2
- Standard Appliqué Colors..... Page 2
- Custom Appliqué Process
  - Appliqué Color Match Process.....Page 2
  - Appliqué Logo Match Process..... Page 3
- Stand-alone Prism Face Plates – Retrofit..... Page 4
- Appliqués Only – Prismapp.....Page 4

## Prism – Architechural Ceiling Diffuser

Krueger's Prism™ ceiling diffuser provides form and functionality for both architects and engineers. This designer ceiling diffuser provides excellent room air mixing and will lend itself to your specific application, offering 9 standard colored appliqué. The Prism's most exceptional trait is that it offers custom match appliqué, which are available in any color or 2, 3 and 4 color logos.

- Appliqué Texture – The Prism Appliques utilize a polycarbonate matte finish. The matte finish will not look identical to a semigloss paint sample or high gloss print. The British White and Off White Appliqués will have a different appearance than the British White or Off White Prism diffusers they are mounted on.
- Appliqué Intended Use – The appliqué was designed to offer the customer not only a color contrast, but a texture contrast as well. Krueger opted not to use a semigloss color for the Appliqués because of concerns with light reflection and glare.

## Standard Appliqué Colors

- Krueger offers nine standard appliqué colors. These colors were derived from the Pantone® PMS color match system. Prism diffusers with standard appliqué colors are available on 4-week standard leadtime and 2-week quick ship.
  - 00 – British White
  - 01 – Off White
  - 02 – Light Grey
  - 03 – Medium Grey
  - 04 – Light Beige
  - 05 – Medium Beige
  - 06 – Blue/Grey
  - 07 – Olive
  - 08 – Rust

## Custom Appliqué Processes

### Color Match Process

- The Krueger rep is responsible for mailing (2) color samples to the Krueger Application Engineer.
  - Attn: GRD Application Engineer  
1401 N. Plano Rd  
Richardson, TX 75081

- The color samples must be at least 2" x 2".
- The color sample will be scanned into a high tech color spectrometer to obtain the initial color match. Then the first round appliqué sample will be reviewed and compared to the color sample sent by the Krueger representative. This extra step will insure a consistent color match every time.
- The order leadtime will start when the Krueger Application Engineer has received the (2) color samples and Krueger Order Entry has received an order.
- Add 1-week to the standard 4-week leadtime for order processing. Total leadtime will be 5-weeks.
- Quick ship orders not available.

### Logo Match Process

- The Krueger rep is responsible for sending the Krueger Application Engineer the logo, company emblem or icon. There are two ways to send Krueger this information.
  - **Disk**  
3.5" Diskette, Zip Disks (100 / 250), or CD Rom
  - **Email**  
[nthomas@krueger-hvac.com](mailto:nthomas@krueger-hvac.com) or [choffmann@krueger-hvac.com](mailto:choffmann@krueger-hvac.com)
- The electronic file must be in one of the following formats (Appliqué – Nom 4" x 4" color or logo insert intended):
  - IBM/PC Platform / Programs Supported
    - Corel Draw 10.0
    - Adobe Illustrator 8.0
    - Adobe PageMaker 6.5
    - PhotoShop 5.0
    - CAD files please save as DXF to be placed in Corel Draw
  - Macintosh Platform / Programs Supported
    - Adobe Illustrator 8.0 / 9.0
    - Adobe PageMaker 6.5
    - Freehand 8.0 / 9.0
    - QuarkXPress 4.04
    - PhotoShop 5.0.2

- Art Files Must Include:
  - File or Files Containing the Design
  - All supporting EPS, TIFF Files Included in the Design
  - All Fonts Used in the Design, Both Screen and Printer Versions
  - Hard Copy or Proof of the Design
  - 4/C Process Designs Must Be Scanned at 300DPI
  - No 4/C Process Supported on IBM Platform
- Add 1-week to the standard 4-week leadtime for order processing. Total leadtime will be 5-weeks.
- Quick ship orders not available

### **Stand-alone Prism Face Plates – Retrofit**

Krueger offers the Prism face plate as a separate item for retrofit applications. The Prism face plate will include standard spring clips for easy change out in the field. You will not receive a backpan when you order the stand-alone Prism face plate.

The Prism face plate will retrofit to most standard layin perforated ceiling diffuser backpans currently installed and availbe in the market today. Contact your local Krueger representative for a spec sheet.

### **Appliqués Only – Prismapp**

Prism Appliqués (Prismapp) are available stand-alone part to replace existing Appliqués in the field.

Looking to change your décor? The Prism diffusers will change with you. Order new and different colored or logo appliqués to replace existing colors. As your walls and carpet change colors through remodeling, order new appliqués to match your décor.

**For more information on this exciting new diffuser, please contact your local Krueger representative today.**