


**KBM - AIR HANDLER, MODULAR**

COIL CONNECTION LOCATION - 1 ROW WATER COIL IN PRE-HEAT WITH DX COIL IN COOLING

**SUBMITTAL SHEET**


COIL 2																
SIZE	3 ROW				4 ROW				6 ROW				8 ROW			
	A	B	C	D	A	B	C	D	A	B	C	D	A	B	C	D
02	6-1/4 [159]	16-3/4 [425]	9-1/2 [241]	4-1/4 [108]	6-1/4 [159]	16-3/4 [425]	9-1/2 [241]	5 [127]	6-1/4 [159]	16-3/4 [425]	9 [229]	5 [127]	6-1/4 [159]	16-3/4 [425]	9 [229]	5 [127]
03	6-1/4 [159]	16-3/4 [425]	9-1/2 [241]	4-1/4 [108]	6-1/4 [159]	16-3/4 [425]	9-1/2 [241]	5 [127]	6-1/4 [159]	16-3/4 [425]	9 [229]	5 [127]	6-1/4 [159]	16-3/4 [425]	9 [229]	5 [127]
04	6-1/2 [165]	17 [432]	9-1/2 [241]	4-3/4 [121]	6-1/2 [165]	17 [432]	9-1/2 [241]	5-1/4 [134]	6-1/2 [165]	17 [432]	9 [229]	5-1/4 [134]	6-1/2 [165]	17 [432]	9 [229]	5-1/2 [140]
06	6-1/2 [165]	24-1/2 [622]	9-1/2 [241]	4-3/4 [121]	6-1/2 [165]	24-1/2 [622]	9-1/2 [241]	5-1/2 [140]	6-1/2 [165]	24-1/2 [622]	9 [229]	6-3/4 [172]	6-1/2 [165]	24-1/2 [622]	9 [229]	5-1/2 [140]
08	6-3/4 [171]	29-3/4 [756]	9-1/2 [241]	4-3/4 [121]	6-3/4 [171]	29-3/4 [756]	9-1/2 [241]	5-1/2 [140]	6-3/4 [171]	29-3/4 [756]	9 [229]	5-1/2 [140]	6-3/4 [171]	29-3/4 [756]	9 [229]	5-1/2 [140]
10	7-1/4 [185]	29-1/2 [749]	9-1/2 [241]	4-3/4 [121]	7-1/4 [185]	29-1/2 [749]	9-1/2 [241]	5-1/2 [140]	7-1/4 [185]	29-1/2 [749]	9 [229]	5-1/2 [140]	7-1/4 [185]	29-1/2 [749]	9 [229]	5-1/2 [140]
12	7-1/4 [185]	35-1/4 [895]	9-1/2 [241]	5-3/4 [147]	7-1/4 [185]	35-1/4 [895]	9-1/2 [241]	6-1/4 [159]	7-1/4 [185]	35-1/4 [895]	9 [229]	6-1/2 [166]	7-1/4 [185]	35-1/4 [895]	9 [229]	6-1/4 [159]
14	7-1/4 [185]	37-3/4 [959]	9-1/2 [241]	5-3/4 [147]	7-1/4 [185]	37-3/4 [959]	9-1/2 [241]	6-1/2 [166]	7-1/4 [185]	37-3/4 [959]	9 [229]	7-1/2 [191]	7-1/4 [185]	37-3/4 [959]	9 [229]	7-3/4 [197]
17	7-1/2 [191]	38 [965]	9-1/2 [241]	6 [153]	7-1/2 [191]	38 [965]	9-1/2 [241]	6-3/4 [172]	7-1/2 [191]	38 [965]	9 [229]	8 [204]	7-1/2 [191]	38 [965]	9 [229]	7 [178]

**NOTES:**

- ALL DIMENSIONS ARE INCHES [MM]
- ALL DIMENSIONS ARE ±1/8" [3]
- METRIC VALUES ARE SOFT CONVERSION
- LIQUID LINE CONNECTION IS LOCATED INSIDE OF CABINET; FIELD PENETRATION OF CABINET IS REQUIRED
- SEE SELECTION PROGRAM FOR CONNECTION SIZES
- DX COILS ARE ONLY AVAILABLE IN 3, 4, 6, OR 8 ROWS
- HOT WATER COILS ARE ONLY AVAILABLE IN 1, 2, 3, OR 4 ROWS
- MODULES FCM AND VCM CAN HAVE UP TO A TOTAL OF 8 ROWS OF COIL
- MODULE MCM CAN HAVE UP TO A TOTAL OF 10 ROWS OF COIL

Revision Date: 12/14

Form: AHMS05-WC14

Replaces: NEW